





OIML Member State

Czech Republic

OIML Certificate No. R49/2013-A-CZ1-24.02

OIML CERTIFICATE ISSUED UNDER SCHEME A

OIML Issuing Authority

Name: Czech Metrology Institute

Address: Okružní 31, 638 00 Brno, Czech Republic

Person responsible: Jan Kalandra

Applicant

Name: GWF AG

Address: Obergrundstrasse 119, CH-6005 Luzern, Switzerland

Manufacturer

Name: GWF AG

Address: Obergrundstrasse 119, CH-6005 Luzern, Switzerland

Identification of the certified type (the detailed characteristics will be defined in the additional pages)

Water meter - ultrasonic, dry dial

sonico NANO

Designation of the module (if applicable)

This OIML Certificate attests the conformity of the above identified type (represented by the sample(s) identified in the OIML type evaluation report) with the requirements of the following Recommendation of the International Organization of Legal Metrology (OIML):

OIML R 49 Edition (year): 2013

For accuracy class (if applicable): 2



This OIML Certificate relates only to metrological and technical characteristics of the type of measuring instrument covered by the relevant OIML Recommendation identified above.

This OIML Certificate does not bestow any form of legal international approval.

The conformity was established by the results of tests and examinations provided in the associated OIML type evaluation report:

- No. 0511-ER-V061-23 dated 29 May 2024 that includes 32 pages including annex 1.
 - Test report No. 6015-PT-P5006-24 that includes 206 pages including annex 1-2.
 - Test report No. 6011-PT-SW008-24 that includes 7 pages including annex 1-2.

The technical documentation relating to the identified type is contained in documentation file:

0511-UL-V061-23

OIML Certificate History

Revision No.	Date	Description of the modification
-	6 June 2024	Issuing certificate

The OIML Issuing Authority

RNDr. Pavel Klenovský Head of Certification Body

Date: 6 June 2024

Cesting Tological Marketing Tological Marketin

Kenny

Important note:

Apart from the mention of the Certificate's reference number and the name of the OIML Member State in which the Certificate is issued, partial quotation of the Certificate and of the associated OIML type evaluation report(s) is not permitted, although either may be reproduced in full.

Measuring system description

The water meters type sonico NANO are designed to measure, memorise and display the volume at metering conditions of water passing through the measurement transducer.

The water meters type sonico NANO are ultrasonic water meters with an electronic indicating device.

The water meters type sonico NANO consist of a cast brass body with connecting screw threads, one pair of ultrasonic transducers and the electronic indicating device. The electronic indicating device is formed by LCD display shown volume and flow. The water meter displays the volume resolution of 0.00001 m³ on the digital display. Water meter is without any buttons with LCD display. Legally non-relevant part of communication with meter is possible by NFC sensor connected on the register.

Ultrasonic water meter has a separation of software. Non-legally relevant parts have no inadmissible influence on legally relevant software, measured data or specific parameters.

The version of SWs and CRCs are displayed in the auto-rounding menu on LCD display in the time period in the form:

- CRC of legally relevant part
- SW version of legally relevant part

The water meters type sonico NANO displays the indication of each volume on the display every two minutes – separately delivered volume for reverse flow and separately delivered volume for forward flow. The permanently shown delivered volume is the difference between two delivered volumes (for reverse and forward flow).

The water meters type sonico NANO can be equipped by impulse module which is not part of this certificate.

The water meters type sonico NANO are by powered mains battery 3.6V.

The water meters shall be installed to operate in any positions.

Marking and inscriptions

The water meters types sonico NANO shall be clearly and indelibly marked with the following information:

- Water meter type
- Unit of measurement (m3)
- Numerical value Q3 in m3/h (Q3 ×.×) and the ratio Q3 / Q1,
- Manufacturer's name, registered trade name or registered trade mark
- Year of manufacture, two last digits of the year of manufacture, or the month and year of manufacture
- Serial number (as near as possible to the indicating device)
- Direction of flow, by means of an arrow (on display)
- Maximum admissible pressure (MAP ××)
- The temperature class $(T \times \times)$
- The pressure loss class ($\Delta p \times \times$)
- The installation sensitivity class (Ux Dx)
- Power voltage
- Environmental classification (M)
- Electromagnetic environmental class (E1)
- Software version
- Hardware version
- Type approval sign according to national regulations

These markings shall comply with the requirements of OIML R 49 and shall be visible without dismantling the water meter after the instrument has been placed on the market or put into use.

Characteristics

Basic technical data of water meters types sonico NANO:

Manufacturer:	GWF AG
Model name:	sonico NANO



Nominal diameter:	15	20
Type details:		
Q_1 [m ³ /h]:		
Q_2 [m ³ /h]:	florrentes are sharen in Table D	
Q ₃ [m3/h]:	Shown in Table 8: $\leq 1000^{-1}$ fo	asic metrological data (flowrates) r Q₃=2.5m³/h
Q ₄ [m ³ /h]:	$\leq 630^{-1}$ for	$Q_3=1.6$ m ³ /h
Q_3/Q_1 :		
Q ₂ /Q ₁ :		1.6
Q ₄ /Q ₃ :	1	.25
Measuring principle:	ultra	asonic
Accuracy class:		2
Maximum permissible error for the lower flowrate zone (MPE _l):	±:	5 %
Maximum permissible error for the upper flowrate zone (MPE _u):	± 2 % for water having ± 3 % for water having	g a temperature ≤ 30 °C g a temperature > 30 °C
Temperature class:	Т	750
Water pressure class:	MA	AP16
Pressure loss class:	Q ₃ 1.6 Δ <i>p10</i> Q ₃ 2.5 Δ <i>p16</i>	Q ₃ 2.5 Δp16 Q ₃ 4.0 Δp25
Reverse flow:	designed	to measure
Environmental class:		M
Electromagnetic environment:	1	E2
Maximum admissible temperature [°C]:	4	50
Maximum admissible pressure [MPa]:	1	6
Orientation limitation:	a	ny
Indicating range – testing mode/user mode [m³]:	9 999 /	999 999
Resolution of the indicating device testing mode/user mode [m³]:	0.0000	1 /0.001
Resolution of the device for rapid testing [pulse/dm³]:	1	00
Resolution of the indicating device for rapid testing [m³]:	0.00	00001
EUT testing requirements (OIML R 49-2:2	013, 8.1.8):	
Category:]	В
Case:]	В
Installation details:		
Connection type (screw thread):	NPSM or G type 3/4", 7/8", 1"	NPSM or G type 7/8", 1", 1 1/4"
Minimum straight length of inlet pipe [mm]:	(0
Minimum straight length of outlet pipe [mm]:	(0
Flow profile sensitivity class:	U0	DD0
Flow conditioner (details if required):	N	To .
Mounting:		-

Orientation:	Any	
Other relevant information:	-	
Length [mm]:	≥ 105mm	≥ 105mm
Reed switch power supply $(U_{\text{max}} / I_{\text{max}})$:	-	
Reed switch K-factor (impulse / L):	-	
Installation details (electrical):		
Wiring instructions:	-	
Mounting arrangement:	-	
Orientation limitations:	-	
Power supply:		
Type (battery, mains AC, mains DC):	Battery	
U_{\max} (V):	3.6	
U_{\min} (V):	1.9	
Frequency:	-	
Minimum battery life time [years]:	16 years	
Software version (of legally relevant SW):	0.6.28	
CRC checksum (of legally relevant SW):	0x854EBACI 0x13372073	
Information specified by the manufact	urer (information in the table below	w are not certified)
-	-	

The ratio Q_3/Q_1 shall be chosen according to paragraph 4.1.4 of OIML R 49-1:2013

Basic metrological data (flowrates)

Manufacturer:	GWF	AG										
Model name:	sonico	NANO										
Nominal diameter:						1	5					
Type details:												
Q_1 [m ³ /h]:	0.040	0.063	0.032	0.050	0.025	0.040	0.020	0.031	0.016	0.025	0.013	0.020
Q_2 [m ³ /h]:	0.064	0.100	0.051	0.080	0.041	0.064	0.032	0.050	0.026	0.040	0.021	0.032
Q_3 [m ³ /h]:	1.600	2.500	1.600	2.500	1.600	2.500	1.600	2.500	1.600	2.500	1.600	2.500
$Q_4 [m^3/h]$:	2.000	3.125	2.000	3.125	2.000	3.125	2.000	3.125	2.000	3.125	2.000	3.125
Q_3/Q_1 :	4	0	5	0	6	3	8	0	1(00	12	25

Manufacturer:	GWF	AG										
Model name:	sonico	NANO										
Nominal diameter:						1	5					
Type details:												
Q_1 [m ³ /h]:	0.010	0.016	0.008	0.013	0.006	0.010	0.005	0.008	0.004	0.006	0.003	0.005
$Q_2 [m^3/h]$:	0.016	0.025	0.013	0.020	0.010	0.016	0.008	0.013	0.006	0.010	0.005	0.008
$Q_3 [m^3/h]$:	1.600	2.500	1.600	2.500	1.600	2.500	1.600	2.500	1.600	2.500	1.600	2.500
$Q_4 [m^3/h]$:	2.000	3.125	2.000	3.125	2.000	3.125	2.000	3.125	2.000	3.125	2.000	3.125
Q_3/Q_1 :	16	50	20	00	25	50	31	15	4(00	5(00



Manufacturer:	GWF A	AG			
Model name:	sonico l	NANO			
Nominal diameter:					15
Type details:					
Q_1 [m ³ /h]:	0.0025	0.004	0.003	0.0025	
Q_2 [m ³ /h]:	0.004	0.006	0.005	0.004	
Q_3 [m ³ /h]:	1.600	2.500	2.500	2.500	
Q_4 [m ³ /h]:	2.000	3.125	3.125	3.125	
Q_3/Q_1 :	63	0	800	1000	

Manufacturer:	GWF	AG										
Model name::	sonico	NANO										
Nominal diameter:						2	0.					
Type details:												
Q_1 [m ³ /h]:	0.063	0.100	0.050	0.080	0.040	0.064	0.031	0.050	0.025	0.040	0.020	0.032
Q_2 [m ³ /h]:	0.100	0.160	0.080	0.128	0.064	0.102	0.050	0.080	0.040	0.064	0.032	0.051
Q_3 [m ³ /h]:	2.500	4.00	2.500	4.00	2.500	4.00	2.500	4.00	2.500	4.00	2.500	4.00
$Q_4 [m^3/h]$:	3.125	5.00	3.125	5.00	3.125	5.00	3.125	5.00	3.125	5.00	3.125	5.00
Q_3/Q_1 :	4	0	5	0	6	3	8	0	10	00	12	25

Manufacturer:	GWF	AG										
Model name::	sonico	NANO										
Nominal diameter:						2	0					
Type details:												
Q_1 [m ³ /h]:	0.016	0.025	0.013	0.020	0.010	0.016	0.008	0.013	0.006	0.010	0.005	0.008
Q_2 [m ³ /h]:	0.025	0.040	0.020	0.032	0.016	0.026	0.013	0.020	0.010	0.016	0.008	0.013
Q_3 [m ³ /h]:	2.500	4.00	2.500	4.00	2.500	4.00	2.500	4.00	2.500	4.00	2.500	4.00
$Q_4 [m^3/h]$:	3.125	5.00	3.125	5.00	3.125	5.00	3.125	5.00	3.125	5.00	3.125	5.00
Q_3/Q_1 :	16	50	20	00	25	50	31	5	4(00	5(00

Manufacturer:	GWF A	AG		
Model name:	sonico	NANO		
Nominal diameter:				
Type details:				
Q_1 [m ³ /h]:	0.004	0.006	0.005	0.004
Q_2 [m ³ /h]:	0.006	0.010	0.008	0.006
Q_3 [m ³ /h]:	2.500	4.00	4.00	4.00
$Q_4 [m^3/h]$:	3.125	5.00	5.00	5.00
Q_3/Q_1 :	63	30	800	1000

Securing components and verification marks

The sonico NANO meters have to be sealed by connecting the plastic seal on the plastic meter cover. The plastic seal is part of the body of the water meter in the form of a plastic frame that holds glass of display on the body of the water meter. The water meter cannot be accessed without damaging seal.



Figure: 1 View on water meter types sonico NANO, display, sealing - example



Figure: 2 Water meter types sonico NANO – description of display



